



Designed to Survive®

Product Inspection Systems for the Pharmaceutical, Nutraceutical and Medical Device Industry

Insight Pharmaceutical Metal Detector

The flagship compact Insight Pharmaceutical Metal Detector offers advanced detection performance, construction quality and reliability characteristics, making it an effective inspection solution for the high-speed elimination of metal contaminants in any capsules, tablets, soft and hard caps after the tablet press and de-dusting processes.

Fits these Applications:



Tablets



Capsules



Soft Gels



Lozenges

Intuitive

The user interface is simple to use, with a huge choice of language options.

Innovative

Its streamline design makes the unit faster to wash down and sterilise between product changeovers, which has long been a sabotage of operational efficiency.

Capability

The detector and reject is able to process up to 30,000 tablets a minute; It is designed to keep pace with any future processing equipment



Robust

The 304 stainless steel easy-clean polished frame ensures stress free cleaning

Flexible

The frame is adjustable via height, width and angle of tilt via a gas strut and has a new clamping sleeve, ensuring the unit can be moved and be up running within minutes.

Rejection of Products

Available with 12 different reject options, the Insight Pharmaceutical is ideally suited to a wide range of site and process requirements. Each reject system is designed to eject the minimal product when contamination is detected and each reject can be removed for cleaning without the use of tools. To accommodate high potency preparations, wash-in-place (WIP) and dust-tight (DT) metal detectors are fitted with dust-tight and water-tight product chutes and reject systems. The WIP and DT reject enables use with highly potent formulations.



Lift flap



Wash in place



Dust-tight



Diverter (Failsafe)

Insight Vertical Fall Pharmaceutical Metal Detector

The quality of finished product can only be guaranteed if incoming and in-process materials are effectively screened to remove all unwanted metallic particles. Vertical Fall metal detectors are recommended to inspect incoming raw materials in free-falling powder or granular form and to inspect formulations prior to tableting or encapsulation.

Fits these Applications:



Powders



Granules

Friendly

Auto-learn and automatic product tracking for user-friendly operation

Throughput

Inspect up to 3000 KG per hour

Accurate

Best in class detection to magnet and non-magnetic metals

Reliable

Up to 8000 data events can be stored and retained even during power interruptions

Compliance

The unit includes standard failsafe, reject confirmation, air failure, audible alarm and reset key switch



Rejection of Products

There are two different reject systems available to ensure contaminants are safely and reliably rejected from the production line. The Sealed Valve Reject is completely dust-tight thus eliminating any cross contamination. The Cowbell-type diverter style reject will reject contaminated product into a separate reject bin.



Sealed Valve Reject



Cowbell Diverter Reject

Insight BottleChek Metal Detector Conveyor

The BottleChek Metal Detector Conveyor inspects bottles or vials at the end of the packaging line for unwanted metallic particles. Deployment of the reject system takes place without causing bottle damage or product loss in the event of metal contamination being detected.

Fits these Applications:



Bottled Products



Vials



Tubs

Adaptable


Our true multi-frequency adapts to new product and packaging in seconds

Robust

The specially design conveyor easily integrates into a production line where side-to-side bottle transfer of the smallest bottles is achieved with complete accuracy

Versatile

The bottle check can be specified with a variety of head sizes to suit customer requirements



Flexible

Available with a full range of systems and reject options: including full fail-safe specification comprising reject confirmation, air failure alarm and bin full alarm

Rejection of Products

The Insight BottleChek is available with different reject options: A Reject Tray where rejected product is pushed off the production line into a stainless steel tray, a standard, lockable reject bin or a side-by-side transfer to another conveyor belt.



Stainless Steel Reject Tray



Reject Bin

Checkweighing

Checkweighing is a method of safe guarding for product weights. A Checkweigher system will check weights of products whilst in motion, rejecting any products that are over or under the set weight. All our Checkweigher systems are approved to both OIML and MID (EC TAC) specifications and include Automatic Mean Weight correct, which helps to ensure weight legislation.

Fits these Applications:



Blister Packs



Packaged Goods



Sachets

Simple operation with colour touchscreen

Type in your product details, initiate setup, and pass a pack several times and the CW3 is automatically set-up and ready to use for average or mean weights.

Fast and Accurate Setup

Type in your product details, initiate setup, and pass a pack several times and the CW3 is automatically set-up and ready to use for average or mean weights.

Save Money, Reduce Product Give Away

Using a highly reliable loadcell technology the CW3 gives you accurate readings while minimizing unnecessary product give away.



X-Ray Inspection

X-Ray Inspection system offers complete quality assurance protection, allowing manufacturers to 'see' inside packages and perform a variety of checks including, fill level, mass measurement and component counting. Metal packaging will have no effect on the X-Ray detection levels so is ideal for inspecting blister packs, metallised or aluminum lids of vials or bottles. Furthermore, an X-Ray Inspection system will not just identify metal but also glass, and dense plastic and rubber.

Fits these Applications:



Blister Packs



Packaged Goods



Sachets

Designed with new Users of X-Ray in mind

A simplified yet powerful inspection feature set, plug & play installation, reliable inspection & low cost of ownership makes the X5c an ideal choice for those switching to X-Ray for the first time.

Get Inspecting Fast with Loma's Product Learn Wizard

A set-up wizard automatically optimises the X5c for each product type & allows you to learn or allows you to learn or switch to new products within minutes.



Quick release belt


No tools required for easy cleaning.



USE YOUR HEAD *with* our Search Head Exchange Program

Upgrade your Met 30 and Met 30+ Pharmaceutical Metal Detector head to the next generation to receive these great benefits from our latest search head model:

- Advancements on the stability of the head which reduces false rejects and improves detection performance
- No graphite within the head which enhances longevity and reduce service costs
- Fully serviced with new product chute, head cable and Calibration Report
- Cost effective route to take advantage of new technology
- 12 month warranty



The new Metal Detector head will be mounted on your current frame and will utilize your current reject system, thus maintaining the same serial number and software versions to minimize any validation requirements. With stock of heads and mounting in our global service centers, we can offer very quick turnarounds.

Worldwide Locations

Headquartered in the UK, LOMA SYSTEMS operates from several locations in the Americas, Europe and Asia. Across these sites LOMA conducts ongoing research and development, specialised manufacturing, sales and service support. Through a worldwide network of OEM and distributor partners, LOMA supplies and supports inspection equipment in over 100 other countries.



Farnborough, UK



Manchester, UK



Helmond, Netherlands



Chicago, USA



Plzen, Czech Republic



Shanghai, China



Sao Paulo, Brazil



Nantes, France



Dinslaken, Germany



Warsaw, Poland

About LOMA SYSTEMS

Established in 1969 in the UK, LOMA SYSTEMS designs, manufactures and supports inspection equipment used to identify contaminants and product defects within the food, packaging and pharmaceutical industries, principally offering Metal Detectors, Checkweighers and X-Ray Inspection systems.

With the addition of the LOCK Inspection, Cintex and Brapenta brands and products, LOMA's reputation is based on consistent quality and advanced technology, the result of continuous and far-reaching research and development programmes. Short lead times, modular design and excellent availability of spare parts, coupled with our passion for customer service, allows our customers to:

- Comply with, and exceed, product safety standards, weight legislation and retailer codes of practice
- Maximise production up-time
- Be self-sufficient
- Lower lifetime costs

We are part of Illinois Tool Works (ITW), a global Fortune 250 diversified industrial manufacturer of value added consumables and speciality equipment with related service businesses. Operating under the core philosophies of 80/20 business processes, customer-back innovation and a decentralized entrepreneurial culture, ITW's seven industry-leading segments leverage the ITW business model to generate solid growth with best-in-class margins and returns in markets where highly innovative, customer-focused solutions are required. These divisions serve customers and markets around the globe, with significant presence in developed and emerging markets. ITW's revenues totalled US\$13.6 billion in 2016, with more than 50,000 employees worldwide.

Local contact



HOANG LONG
TECHNOLOGY

Always for your product quality



An ITW Company

www.congnghehoanglong.com

Hotline: 0907 686 889 | Email: hoanglongtechnology@gmail.com

Metal Detection | Checkweighing | X-Ray Inspection

Loma Systems is a registered trademark of Illinois Tool Works Inc. (ITW). Other names, logos, icons and marks identifying our products and services referenced herein are trademarks of ITW and may not be used without the prior written permission of ITW. Other product and company names listed are trademarks or trade names of their respective companies. Copyright © 2016 Illinois Tool Works Inc. All rights reserved. All of the specifications shown in this document are subject to change without notice.

PHEN_893201705

In association with

